

SDN12483816PL Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 48 x 37 x 16in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDN12483816PL>

Technical Specifications

Brand	Wiegmann
Item	Disconnect enclosure
Slope Top	No
Vented	No
NEMA Rating	12/13
Disconnect Mounting	Right flange
Nominal Enclosure Dimensions	48 x 37 x 16in (HxWxD)
Enclosure Height	48.00in
Enclosure Width	37.38in
Enclosure Depth	16.88in
Mounting	Wall

Integral Mounting Feet	Yes
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Cover Type	Single-door
Hinge Type	Continuous hinge
Number of Hinges Per Door	1
Latch Type	3-point padlocking handle
Padlockable	Yes
Keylocking	No
Subpanel	Purchase subpanel separately

Agency Approvals

UL Listed File #	E64791
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SDN12483816PL.pdf>
See store item page for other formats.