

SE-ANT150 Cut Sheet

STRIDE dome LTE antenna, IP67, panel mount, 9.8ft/3m cable length. For use with SE-SL3011-4G and SE-SL3011-4GG VPN routers.



For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-ANT150>

Technical Specifications

Brand	STRIDE
Item	LTE antenna
Antenna Type	Dome
Antenna Connector	SMA (M)
Frequency Range	700-960 MHz / 1.71-2.7 GHz
Gain	1.2 dBi / 3.2 dBi
Maximum Power	5W
Height	1.89in
Mounting	Panel
Cable Length	9.8ft/3m
IP Rating	IP67
For Use With	SE-SL3011-4G and SE-SL3011-4GG VPN routers
Application	LTE, CDMA, GSM, HSPA, UMTS

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
RoHS Status	No
EU REACH	View EU REACH document