

SE-MC2U-SC Cut Sheet



STRIDE industrial unmanaged Ethernet media converter, 2 ports, (1) Ethernet 10/100Base-T (RJ45) and (1) multi-mode SC 100FX fiber port(s), -10 to +60 deg C, plastic housing, IP40, 35mm DIN rail mount, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-MC2U-SC>

Technical Specifications

Brand	STRIDE
Item	Ethernet media converter
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	2
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (1) Ethernet 10/100Base-T (RJ45)• (1) multi-mode SC 100FX fiber
Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps auto-detect• 100 Mbps fiber
Operating Temperature	-10 to +60 deg C
Housing Material	Plastic
IP Rating	IP40
Mounting	35mm DIN rail
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SE-MC2U-SC.pdf>
See store item page for other formats.