

SE-MC2U-ST Cut Sheet



STRIDE industrial unmanaged Ethernet media converter, 2 ports, (1) Ethernet 10/100Base-T (RJ45) and (1) multi-mode ST 100FX fiber port(s), -10 to +60 deg C, plastic housing, IP40, 35mm DIN rail mount, hazardous location rated.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-MC2U-ST>

Technical Specifications

| | |
|---|--|
| Brand | STRIDE |
| Item | Ethernet media converter |
| Grade | Industrial |
| Switch Type | Unmanaged |
| Number of Ports | 2 |
| Communication Port and Connection Type(s) | <ul style="list-style-type: none">• (1) Ethernet 10/100Base-T (RJ45)• (1) multi-mode ST 100FX fiber |
| Port Speed(s) | <ul style="list-style-type: none">• 10/100 Mbps auto-detect• 100 Mbps fiber |
| Operating Temperature | -10 to +60 deg C |
| Housing Material | Plastic |
| IP Rating | IP40 |
| Mounting | 35mm DIN rail |
| Application | Hazardous location rated |

Agency Approvals

| | |
|----------------------|--|
| UL Listed File # | E200031 |
| UL Recognized File # | None |
| UL Hazardous File # | E200031 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SE-MC2U-ST.pdf>
See store item page for other formats.