

# SE-SL3001 Cut Sheet



StrideLinx Basic industrial VPN router, wired Internet connectivity, (5) Ethernet Gigabit (RJ45) port(s), Android/iOS with mobile VPN, 12-24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SL3001>

## Technical Specifications

<b>Brand</b>	StrideLinx	<b>Operating Temperature</b>	-20 to +65 deg C
<b>Item</b>	Router	<b>Housing Material</b>	Metal
<b>Series</b>	Basic	<b>IP Rating</b>	IP20
<b>Grade</b>	Industrial	<b>Mounting</b>	35mm DIN rail
<b>Router Type</b>	VPN	<b>External Power Requirement</b>	12-24 VDC
<b>Internet Connectivity</b>	Wired	<b>Firewall</b>	SPI
<b>Number of Ports</b>	5	<b>Interface</b>	Browser (non-secure) and mobile app
<b>Communication Port and Connection Type(s)</b>	(5) Ethernet Gigabit (RJ45)	<b>Mobile App Enabled</b>	Android/iOS with mobile VPN
<b>Port Speed(s)</b>	10/100/1000 Mbps auto-detect	<b>Includes</b>	10 GB monthly bandwidth per StrideLinx company account
<b>Input Control</b>	(1) digital input for local control		

## Agency Approvals

<b>UL Listed File #</b>	E495151
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SE-SL3001.pdf>  
See store item page for other formats.