

SE-SL3011 Cut Sheet



StrideLinx Pro industrial VPN router, wired Internet connectivity, (5) Ethernet Gigabit (RJ45) port(s), MQTTs, Android/iOS with mobile VPN, 12-24 VDC required.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SL3011>

Technical Specifications

Brand	StrideLinx
Item	Router
Series	Pro
Grade	Industrial
Router Type	VPN
Internet Connectivity	Wired
Number of Ports	5
Communication Port and Connection Type(s)	(5) Ethernet Gigabit (RJ45)
Port Protocol(s)	<ul style="list-style-type: none">• MQTTs Client• webserver (non-secure HTTP)
Port Speed(s)	10/100/1000 Mbps auto-detect
Input Control	(1) digital input for local control
Operating Temperature	-20 to +65 deg C
Housing Material	Metal
IP Rating	IP20

Mounting	35mm DIN rail
External Power Requirement	12-24 VDC
Firewall	SPI
Interface	Browser (non-secure) and mobile app
Mobile App Enabled	Android/iOS with mobile VPN
Data Cache	8GB (system and I/O data total)
Includes	10 GB monthly bandwidth per StrideLinx company account
Subscription(s) Available	Notify and logging/reporting
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: Yes (not user replaceable)• Packaging Instructions: 970• UN Number: UN3091• Hazard Type: Lithium Batteries• Battery Type: Button• Lithium Content: 0.01

Agency Approvals

UL Listed File #	E495151
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SE-SL3011.pdf>
See store item page for other formats.