

SE-SW5M-2SC Cut Sheet



STRIDE industrial managed Ethernet switch, 5 ports, (3) Ethernet 10/100Base-T (RJ45) and (2) multi-mode SC 100FX fiber port(s), Modbus TCP, -40 to +75 deg C, metal housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW5M-2SC>

Technical Specifications

Brand	STRIDE	Port Speed(s)	<ul style="list-style-type: none">• 10/100 Mbps auto-detect• 100 Mbps fiber
Item	Ethernet switch	Operating Temperature	-40 to +75 deg C
Grade	Industrial	Housing Material	Metal
Switch Type	Managed	IP Rating	IP40
Number of Ports	5	Mounting	35mm DIN rail
Communication Port and Connection Type(s)	<ul style="list-style-type: none">• (3) Ethernet 10/100Base-T (RJ45)• (2) multi-mode SC 100FX fiber	Application	Hazardous location rated
Port Protocol(s)	<ul style="list-style-type: none">• Modbus TCP• webserver (secure HTTPs)		

Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SE-SW5M-2SC.pdf>
See store item page for other formats.