

SE-SW5U Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 5 ports, (5) Ethernet 10/100Base-T (RJ45) port(s), -10 to +60 deg C, plastic housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW5U>

Technical Specifications

| | |
|--|----------------------------------|
| Brand | STRIDE |
| Item | Ethernet switch |
| Grade | Industrial |
| Switch Type | Unmanaged |
| Number of Ports | 5 |
| Communication Port and Connection Type(s) | (5) Ethernet 10/100Base-T (RJ45) |
| Port Speed(s) | 10/100 Mbps auto-detect |
| Operating Temperature | -10 to +60 deg C |
| Housing Material | Plastic |
| IP Rating | IP40 |
| Mounting | 35mm DIN rail |
| Application | Hazardous location rated |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E200031 |
| UL Recognized File # | None |
| UL Hazardous File # | E200031 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |