

SE-SW8M Cut Sheet



STRIDE industrial managed Ethernet switch, 8 ports, (8) Ethernet 10/100Base-T (RJ45) port(s), Modbus TCP, -40 to +75 deg C, metal housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW8M>

Technical Specifications

| | |
|--|----------------------------------|
| Brand | STRIDE |
| Item | Ethernet switch |
| Grade | Industrial |
| Switch Type | Managed |
| Number of Ports | 8 |
| Communication Port and Connection Type(s) | (8) Ethernet 10/100Base-T (RJ45) |
| Port Protocol(s) | Modbus TCP |
| Port Speed(s) | 10/100 Mbps auto-detect |
| Operating Temperature | -40 to +75 deg C |
| Housing Material | Metal |
| IP Rating | IP40 |
| Mounting | 35mm DIN rail |
| Application | Hazardous location rated |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E200031 |
| UL Recognized File # | None |
| UL Hazardous File # | E200031 |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |