

SE-SW8U Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 8 ports, (8) Ethernet 10/100Base-T (RJ45) port(s), -10 to +60 deg C, plastic housing, IP40, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE-SW8U>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	8
Communication Port and Connection Type(s)	(8) Ethernet 10/100Base-T (RJ45)
Port Speed(s)	10/100 Mbps auto-detect
Operating Temperature	-10 to +60 deg C
Housing Material	Plastic
IP Rating	IP40
Mounting	35mm DIN rail
Application	Hazardous location rated

Agency Approvals

UL Listed File #	E200031
UL Recognized File #	None
UL Hazardous File #	E200031
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document