SE3-MC2U-T1-T Cut Sheet

AUTOMATIONDIRECT.com
www.automationdirect.com

STRIDE industrial unmanaged Ethernet media converter, 2 ports, (1) Ethernet 10/100Base-T (RJ45) and (1) multi-mode ST 100FX fiber port(s), (1) Form A (SPST) relay, -40 to +80 deg C, metal housing, IP30, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:

https://www.automationdirect.com/pn/SE3-MC2U-T1-T

Technical Specifications

Brand	STRIDE
Item	Ethernet media converter
Grade	Industrial
Switch Type	Unmanaged
Nominal Input Voltage	12-48 VDC
Number of Ports	2
Communication Port and Connection Type(s)	• (1) Ethernet 10/100Base-T (RJ45) • (1) multi-mode ST 100FX fiber
Communication Standard(s)	• IEEE 802.3 10Base-T • IEEE 802.3u 100Base-TX/FX • IEEE 802.3x Flow Control

Port Speed(s)	• 10/100 Mbps auto-detect • 100 Mbps fiber
Redundant Input Power	Yes
Relay Type	(1) Form A (SPST) relay
Operating Temperature	-40 to +80 deg C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail or panel
Additional Information	Redundant power input design, 12-48 VDC

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings

2D Drawing PDF Link:
https://cdn.automationdirect.com/static/drawings/2d/SE3-MC2U-T1-T.pdf
See store item page for other formats.