

SE3-SW8U-T Cut Sheet



STRIDE industrial unmanaged Ethernet switch, 8 ports, (8) Ethernet 10/100Base-T (RJ45) port(s), -40 to +75 deg C, metal housing, IP30, 35mm DIN rail or panel mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SE3-SW8U-T>

Technical Specifications

Brand	STRIDE
Item	Ethernet switch
Grade	Industrial
Switch Type	Unmanaged
Number of Ports	8
Communication Port and Connection Type(s)	(8) Ethernet 10/100Base-T (RJ45)
Port Speed(s)	10/100 Mbps auto-detect
Nominal Input Voltage	12-48 VDC
Operating Temperature	-40 to +75 deg C
Housing Material	Metal
IP Rating	IP30
Mounting	35mm DIN rail or panel

Agency Approvals

UL Listed File #	E157382
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document