

SEL.10.223 Cut Sheet



SapiSelco general purpose nylon cable tie, 7.87in length, 0.18in width, 48.51 lb tensile strength, 2.01in maximum bundle diameter, red. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.10.223>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Material	Nylon
Length	7.87in
Width	0.18in
Tensile Strength	48.51 lb
Maximum Bundle Diameter	2.01in

Color	Red
UV Resistant	No
Temperature Rating	-40 to +185 °F
Installation Temperature	+14 °F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document