

# SEL.2.205 Cut Sheet



SapiSelco general purpose cable tie, 7.87in length, 0.1in width, 24.25lb tensile strength, 2.17in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.2.205>

---

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	General purpose
<b>Length</b>	7.87in
<b>Width</b>	0.1in
<b>Tensile Strength</b>	24.25lb
<b>Maximum Bundle Diameter</b>	2.17in
<b>Color</b>	Natural
<b>Material</b>	Nylon
<b>Temperature Rating</b>	-40 to +185 deg F
<b>Quantity per Pack</b>	100

---

## Agency Approvals

<b>UL Listed File #</b>	E160935
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>