

SEL.2.431 Cut Sheet



SapiSelco general purpose nylon cable tie, 9.45in length, 0.3in width, 101.43 lb tensile strength, 2.44in maximum bundle diameter, natural. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.2.431>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Material	Nylon
Length	9.45in
Width	0.3in
Tensile Strength	101.43 lb
Maximum Bundle Diameter	2.44in
Color	Natural
UV Resistant	No
Temperature Rating	-40 to +185 °F
Installation Temperature	+14 °F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	100

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document