

SEL.3.304 Cut Sheet



SapiSelco general purpose cable tie, 6.3in length, 0.1in width, 24.25lb tensile strength, 1.65in maximum bundle diameter, black, nylon. Package of 1000.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.3.304>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Length	6.3in
Width	0.1in
Tensile Strength	24.25lb
Maximum Bundle Diameter	1.65in
Color	Black
Material	Nylon
Temperature Rating	-40 to +185 deg F
Quantity per Pack	1000

Agency Approvals

UL Listed File #	E160935
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document