

SEL.3.311 Cut Sheet



SapiSelco general purpose cable tie, 7.87in length, 0.14in width, 33.08lb tensile strength, 2.17in maximum bundle diameter, black, nylon. Package of 1000.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.3.311>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Length	7.87in
Width	0.14in
Tensile Strength	33.08lb
Maximum Bundle Diameter	2.17in
Color	Black
Material	Nylon
UV Resistant	No
Temperature Rating	-40 to +185 deg F
Installation Temperature	+14 deg F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	1000

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document