

SEL.3.321 Cut Sheet



SapiSelco general purpose nylon cable tie, 6.3in length, 0.18in width, 48.51 lb tensile strength, 1.5in maximum bundle diameter, black. Package of 1000.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.3.321>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Material	Nylon
Length	6.3in
Width	0.18in
Tensile Strength	48.51 lb
Maximum Bundle Diameter	1.5in
Color	Black
UV Resistant	No
Temperature Rating	-40 to +185 °F
Installation Temperature	+14 °F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	1000

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document