

# SEL.3.428 Cut Sheet



SapiSelco general purpose cable tie, 16.93in length, 0.18in width, 48.51lb tensile strength, 4.84in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.3.428>

## Technical Specifications

|                          |                                            |
|--------------------------|--------------------------------------------|
| Brand                    | SapiSelco                                  |
| Item                     | Cable tie                                  |
| Cable Tie Type           | General purpose                            |
| Length                   | 16.93in                                    |
| Width                    | 0.18in                                     |
| Tensile Strength         | 48.51lb                                    |
| Maximum Bundle Diameter  | 4.84in                                     |
| Color                    | Black                                      |
| Material                 | Nylon                                      |
| UV Resistant             | No                                         |
| Temperature Rating       | -40 to +185 deg F                          |
| Installation Temperature | +14 deg F                                  |
| Flammability             | UL 94 V-2                                  |
| UL Rating                | UL 62275                                   |
| Applicable Standards     | UL 62275, CSA-C22.2 No 62275 and IEC 62275 |
| Quantity per Pack        | 100                                        |

## Agency Approvals

|                  |                                        |
|------------------|----------------------------------------|
| UL Listed File # | E160935                                |
| CE               | <a href="#">View CE declarations</a>   |
| RoHS Status      | Yes (See CE Doc)                       |
| EU REACH         | <a href="#">View EU REACH document</a> |