

SEL.3.437 Cut Sheet



SapiSelco general purpose cable tie, 21.26in length, 0.3in width, 101.43lb tensile strength, 6.3in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.3.437>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Length	21.26in
Width	0.3in
Tensile Strength	101.43lb
Maximum Bundle Diameter	6.3in
Color	Black
Material	Nylon
UV Resistant	No
Temperature Rating	-40 to +185 deg F
Installation Temperature	+14 deg F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	100

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document