

SEL.3.453 Cut Sheet



SapiSelco general purpose cable tie, 39.37in length, 0.49in width, 216.09lb tensile strength, 11.81in maximum bundle diameter, black, nylon. Package of 50.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.3.453>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	General purpose
Length	39.37in
Width	0.49in
Tensile Strength	216.09lb
Maximum Bundle Diameter	11.81in
Color	Black
Material	Nylon
UV Resistant	No
Temperature Rating	-40 to +185 deg F
Installation Temperature	+14 deg F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	50

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document