

SEL.8.210 Cut Sheet



SapiSelco heat stabilized cable tie, 5.51in length, 0.14in width, 33.08lb tensile strength, 1.42in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.8.210>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Heat stabilized
Length	5.51in
Width	0.14in
Tensile Strength	33.08lb
Maximum Bundle Diameter	1.42in
Color	Natural
Material	Nylon
UV Resistant	No
Temperature Rating	-40 to +221 deg F
Installation Temperature	+14 deg F
Flammability	UL 94 V-2
Quantity per Pack	100

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document