

SEL.9.210 Cut Sheet



SapiSelco heat stabilized nylon cable tie, 5.51in length, 0.14in width, 33.08 lb tensile strength, 1.42in maximum bundle diameter, black. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.9.210>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Heat stabilized
Material	Nylon
Length	5.51in
Width	0.14in
Tensile Strength	33.08 lb
Maximum Bundle Diameter	1.42in
Color	Black
UV Resistant	No
Temperature Rating	-40 to +221 °F
Installation Temperature	+14 °F
Flammability	UL 94 V-2
UL Rating	UL 62275
Applicable Standards	UL 62275, CSA-C22.2 No 62275 and IEC 62275
Quantity per Pack	100

Agency Approvals

UL Listed File #	E160935
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document