

SEL.EC2.211R Cut Sheet



SapiSelco flame retardant cable tie, 7.87in length, 0.14in width, 30.87lb tensile strength, 2.17in maximum bundle diameter, natural, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.EC2.211R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Flame retardant
Length	7.87in
Width	0.14in
Tensile Strength	30.87lb
Maximum Bundle Diameter	2.17in
Color	Natural
Material	Nylon
UV Resistant	No
Temperature Rating	+23 to +140 deg F
Installation Temperature	+32 deg F
Flammability	UL 94 V-0
Quantity per Pack	100

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document