

SEL.ICE.210R Cut Sheet



SapiSelco low temperature UV resistant cable tie, 5.51in length, 0.14in width, 33.72lb tensile strength, 1.41in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.ICE.210R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Low temperature UV resistant
Length	5.51in
Width	0.14in
Tensile Strength	33.72lb
Maximum Bundle Diameter	1.41in
Color	Black
Material	Nylon
Temperature Rating	-58 to +185 deg F
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document