

SEL.ICE.426R Cut Sheet



SapiSelco low temperature UV resistant cable tie, 14.17in length, 0.18in width, 49.45lb tensile strength, 3.97in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.ICE.426R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Low temperature UV resistant
Length	14.17in
Width	0.18in
Tensile Strength	49.45lb
Maximum Bundle Diameter	3.97in
Color	Black
Material	Nylon
Temperature Rating	-58 to +185 deg F
Quantity per Pack	100

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document