

SEL.SUV.223R Cut Sheet



SapiSelco super UV resistant cable tie, 7.87in length, 0.18in width, 48.51lb tensile strength, 2.01in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.SUV.223R>

Technical Specifications

Brand	SapiSelco
Item	Cable tie
Cable Tie Type	Super UV resistant
Length	7.87in
Width	0.18in
Tensile Strength	48.51lb
Maximum Bundle Diameter	2.01in
Color	Black
Material	Nylon
UV Resistant	Yes
Temperature Rating	-40 to +185 deg F
Installation Temperature	-22 deg F
Flammability	UL 94 HB
Quantity per Pack	100

Agency Approvals

CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document