

# SEL.UV2.426 Cut Sheet



SapiSelco UV resistant cable tie, 14.17in length, 0.18in width, 61.73lb tensile strength, 3.98in maximum bundle diameter, black, nylon. Package of 100.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEL.UVV2.426>

## Technical Specifications

<b>Brand</b>	SapiSelco
<b>Item</b>	Cable tie
<b>Cable Tie Type</b>	UV resistant
<b>Length</b>	14.17in
<b>Width</b>	0.18in
<b>Tensile Strength</b>	61.73lb
<b>Maximum Bundle Diameter</b>	3.98in
<b>Color</b>	Black
<b>Material</b>	Nylon
<b>Temperature Rating</b>	-40 to +257 deg F
<b>Quantity per Pack</b>	100

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>