

# SEOOW-12-3BK-1 Cut Sheet



Southwire portable cord, unshielded, SEOOW, 600V, 3 conductors (includes ground), 12 AWG, TPE conductor insulation material, black, white and green, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEOOW-12-3BK-1>

## Technical Specifications

<b>Brand</b>	Southwire	<b>Shielding</b>	Unshielded
<b>Item</b>	Cord	<b>Jacket Material</b>	TPE
<b>Wire/Cable Type</b>	Portable	<b>Jacket Color</b>	Black
<b>UL Wire/Cable Type</b>	SEOOW	<b>Nominal Overall Cable Diameter</b>	0.595in
<b>Applicable Standards</b>	UL 62	<b>Bulk Length</b>	Cut to length
<b>Application</b>	General purpose	<b>Package Type</b>	1 to 50ft = Coil, 51 to 110ft = 14 x 7in Reel, 111 to 150ft = 14 x 10in Reel, 151 to 240ft = 16 x 10in Reel, 241 to 340ft = 18 x 10in Reel, 341 to 440ft = 18 x 13in Reel, 441 to 960ft = 24 x 17in Wooden Reel, 961 to 1580ft = 30 x 17in Wooden Reel, 1581 to MAX = Large Wooden Reel
<b>Flexibility</b>	Flexible		
<b>Voltage Rating</b>	600V		
<b>Conductors</b>	3 conductors (includes ground)		
<b>Conductor Size</b>	12 AWG		
<b>Conductor Stranding</b>	65-stranded		
<b>Conductor Material</b>	Bare copper		
<b>Conductor Insulation Material</b>	TPE		
<b>Conductor Insulation Color</b>	Black, white and green		

## Agency Approvals

<b>UL Listed File #</b>	E46194
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	90458
<b>RoHS Status</b>	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>
<b>Other</b>	<a href="#">RoHS Statement</a>