

SEOOW-14-3BK-1 Cut Sheet



Southwire portable cord, unshielded, SEOOW, 600V, 3 conductors (includes ground), 14 AWG, TPE conductor insulation material, black, white and green, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEOOW-14-3BK-1>

Technical Specifications

Brand	Southwire
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SEOOW
Applicable Standards	UL 62
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V
Conductors	3 conductors (includes ground)
Conductor Size	14 AWG
Conductor Stranding	41-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE
Conductor Insulation Color	Black, white and green

Shielding	Unshielded
Jacket Material	TPE
Jacket Color	Black
Nominal Overall Cable Diameter	0.525in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 140ft = 14 x 7in Reel, 141 to 200ft = 14 x 10in Reel, 201 to 310ft = 16 x 10in Reel, 311 to 440ft = 18 x 10in Reel, 441 to 570ft = 18 x 13in Reel, 571 to 1230ft = 24 x 17in Wooden Reel, 1231 to 2030ft = 30 x 17in Wooden Reel, 2031 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement