


SEOOW-16-4BK-1 Cut Sheet



Southwire portable cord, unshielded, SEOOW, 600V, 4 conductors (includes ground), 16 AWG, TPE conductor insulation material, black, white, red and green, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEOOW-16-4BK-1>

Technical Specifications

Brand	Southwire
Item	Cord
Wire/Cable Type	Portable
UL Wire/Cable Type	SEOOW
Applicable Standards	UL 62
Application	General purpose
Flexibility	Flexible
Voltage Rating	600V
Conductors	4 conductors (includes ground)
Conductor Size	16 AWG
Conductor Stranding	26-stranded
Conductor Material	Bare copper
Conductor Insulation Material	TPE
Conductor Insulation Color	Black, white, red and green

Shielding	Unshielded
Jacket Material	TPE
Jacket Color	Black
Nominal Overall Cable Diameter	0.42in
Bulk Length	Cut to length
Package Type	1 to 50ft = Coil, 51 to 220ft = 14 x 7in Reel, 221 to 310ft = 14 x 10in Reel, 311 to 490ft = 16 x 10in Reel, 491 to 690ft = 18 x 10in Reel, 691 to 890ft = 18 x 13in Reel, 891 to 1930ft = 24 x 17in Wooden Reel, 1931 to 3170ft = 30 x 17in Wooden Reel, 3171 to MAX = Large Wooden Reel

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement