

SEOOW-18-3BK-1 Cut Sheet



Southwire portable cord, unshielded, SEOOW, 600V, 3 conductors (includes ground), 18 AWG, TPE conductor insulation material, black, white and green, TPE jacket, black, cut to length.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SEOOW-18-3BK-1>

Technical Specifications

Brand	Southwire	Shielding	Unshielded
Item	Cord	Jacket Material	TPE
Wire/Cable Type	Portable	Jacket Color	Black
UL Wire/Cable Type	SEOOW	Nominal Overall Cable Diameter	0.365in
Applicable Standards	UL 62	Bulk Length	Cut to length
Application	General purpose	Package Type	1 to 75ft = Coil, 76 to 290ft = 14 x 7in Reel, 291 to 420ft = 14 x 10in Reel, 421 to 650ft = 16 x 10in Reel, 651 to 910ft = 18 x 10in Reel, 911 to 1190ft = 18 x 13in Reel, 1191 to 2550ft = 24 x 17in Wooden Reel, 2551 to 4200ft = 30 x 17in Wooden Reel, 4201 to MAX = Large Wooden Reel
Flexibility	Flexible		
Voltage Rating	600V		
Conductors	3 conductors (includes ground)		
Conductor Size	18 AWG		
Conductor Stranding	16-stranded		
Conductor Material	Bare copper		
Conductor Insulation Material	TPE		
Conductor Insulation Color	Black, white and green		

Agency Approvals

UL Listed File #	E46194
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	90458
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement