

# SF08-M1KTB-B Cut Sheet



Patlite SF series LED audible-visual signal beacon, 86 dB at 1m, continuous tone(s), (22) selectable flashing and rotating patterns, blue, 80mm, 12-24 VDC, IP66, NEMA 4X/13, push-in terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SF08-M1KTB-B>

## Technical Specifications

<b>Brand</b>	Patlite
<b>Item</b>	Audible-visual signal beacon
<b>Series</b>	SF
<b>Bulb Type</b>	LED
<b>Operator Size</b>	80mm
<b>Operator Color</b>	Blue
<b>Light Color(s)</b>	Blue
<b>Light Function</b>	(22) selectable flashing and rotating patterns
<b>Housing Material</b>	Polycarbonate
<b>Material</b>	Polycarbonate

<b>Loudness Decibel</b>	86 dB at 1m
<b>Tone Frequency</b>	2.5 kHz
<b>Tone Type</b>	Continuous
<b>Touch to Acknowledge</b>	No
<b>Voltage Rating</b>	12-24 VDC
<b>Mounting</b>	Base
<b>IP Rating</b>	IP66
<b>NEMA Rating</b>	4X/13
<b>Connection</b>	Push-in terminal

## Agency Approvals

<b>UL Listed File #</b>	E215660
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SF08-M1KTB-B.pdf>  
See store item page for other formats.