

SF08-M1KTB-G Cut Sheet



Patlite SF series LED audible-visual signal beacon, 86 dB at 1m, continuous tone(s), (22) selectable flashing and rotating patterns, green, 80mm, 12-24 VDC, IP66, NEMA 4X/13, push-in terminal.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SF08-M1KTB-G>

Technical Specifications

Brand	Patlite
Item	Audible-visual signal beacon
Series	SF
Bulb Type	LED
Operator Size	80mm
Operator Color	Green
Light Color(s)	Green
Light Function	(22) selectable flashing and rotating patterns
Housing Material	Polycarbonate
Material	Polycarbonate

Loudness Decibel	86 dB at 1m
Tone Frequency	2.5 kHz
Tone Type	Continuous
Touch to Acknowledge	No
Voltage Rating	12-24 VDC
Mounting	Base
IP Rating	IP66
NEMA Rating	4X/13
Connection	Push-in terminal

Agency Approvals

UL Listed File #	E215660
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SF08-M1KTB-G.pdf>
See store item page for other formats.