

SF08-M2KTN-B Cut Sheet



Patlite SF series LED industrial signal beacon, 80mm, blue, (22) selectable flashing and rotating patterns, IP66, NEMA 4X/13, base mount, 100-240 VAC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SF08-M2KTN-B>

Technical Specifications

Brand	Patlite
Item	Industrial signal beacon
Bulb Type	LED
Series	SF
Operator Size	80mm
Operator Color	Blue
Light Color(s)	Blue
Light Function	(22) selectable flashing and rotating patterns

Housing Material	Polycarbonate
Mounting	Base
IP Rating	IP66
NEMA Rating	4X/13
Connection	Push-in terminal
Touch to Acknowledge	No
Voltage Rating	100-240 VAC

Agency Approvals

UL Listed File #	E215660
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SF08-M2KTN-B.pdf>
See store item page for other formats.