

SF10-M2KTN-R Cut Sheet



Patlite SF series LED industrial signal beacon, 100mm, red, (22) selectable flashing and rotating patterns, IP66, NEMA 4X/13, base mount, 100-240 VAC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SF10-M2KTN-R>

Technical Specifications

| | |
|-----------------------|--|
| Brand | Patlite |
| Item | Industrial signal beacon |
| Bulb Type | LED |
| Series | SF |
| Operator Size | 100mm |
| Operator Color | Red |
| Light Color(s) | Red |
| Light Function | (22) selectable flashing and rotating patterns |

| | |
|-----------------------------|------------------|
| Housing Material | Polycarbonate |
| Mounting | Base |
| IP Rating | IP66 |
| NEMA Rating | 4X/13 |
| Connection | Push-in terminal |
| Touch to Acknowledge | No |
| Voltage Rating | 100-240 VAC |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E215660 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SF10-M2KTN-R.pdf>
See store item page for other formats.