

SFC-29-8-10 Cut Sheet



Sung-II Machinery drive coupling, double loop, nickel plated steel, setscrew, size 29, 8 x 10mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFC-29-8-10>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Double loop
Material	Nickel plated steel
Maximum Torque	0.4 N·m
Maximum Angular Misalignment	10 degrees
Maximum Parallel Misalignment	2mm
Maximum RPM	3000

Attachment Style	Setscrew
Coupling Size	29
Overall Length	28mm
Bore Diameter	8mm
Bore Diameter 2	10mm
Outside Diameter	25mm
Clamp Screw Fastening Torque	1.7 N·m
Clamp Screw Size	M4-0.7 x 6mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SFC-29-8-10.pdf>
See store item page for other formats.