

SFC-38-10-10 Cut Sheet



Sung-II Machinery drive coupling, double loop, nickel plated steel, setscrew, size 38, 10 x 10mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFC-38-10-10>

Technical Specifications

| | |
|--------------------------------------|---------------------|
| Brand | Sung-II Machinery |
| Item | Drive coupling |
| Coupling Type | Double loop |
| Material | Nickel plated steel |
| Maximum Torque | 1.4 N·m |
| Maximum Angular Misalignment | 10 degrees |
| Maximum Parallel Misalignment | 2.5mm |
| Maximum RPM | 3000 |

| | |
|-------------------------------------|--------------|
| Attachment Style | Setscrew |
| Coupling Size | 38 |
| Overall Length | 35mm |
| Bore Diameter | 10mm |
| Bore Diameter 2 | 10mm |
| Outside Diameter | 32mm |
| Clamp Screw Fastening Torque | 1.7 N·m |
| Clamp Screw Size | M4-0.7 x 6mm |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SFC-38-10-10.pdf>
See store item page for other formats.