

SFC18KC1234-10 Cut Sheet



Minerallac hammer-on flange clamp conduit hanger assembly, spring clip, back mount, 25 lbs, UL Type UL 2239. Package of 10. For use with 1/8 to 1/4in flanges and 1/2 or 3/4in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFC18KC1234-10>

Technical Specifications

Brand	Minerallac	Rigid Metallic Conduit (RMC) Trade Size	1/2in and 3/4in
Item	Conduit hanger assembly	Electrical Metallic Tubing (EMT) Trade Size	1/2in and 3/4in
Mount Type	Hammer-on flange clamp	Intermediate Metallic Conduit (IMC) Trade Size	1/2in and 3/4in
Hanger Type	Spring clip	Reduced Wall Flexible Metal Conduit Trade Size	3/8in and 1/2in
Mount Side	Back	Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1/2in and 3/4in
Material	Spring steel	UL Type	UL 2239
Finish	Zinc phosphate plated	Quantity per Pack	10
Minimum Flange Thickness	1/8in	For Use With	1/8 to 1/4in flanges and 1/2 or 3/4in conduit
Maximum Flange Thickness	1/4in		
Load Rating	25 lbs		
Outside Diameter	0.70in-1.05in		
Tubing Size	3/4in, 13/16in, 7/8in, 15/16in and 1in		

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document