

SFC516KC1234 Cut Sheet



Minerallac hammer-on flange clamp conduit hanger assembly, spring clip, back mount, 25 lbs, UL Type UL 2239. Package of 100. For use with 5/16 to 1/2in flanges and 1/2 or 3/4in conduit.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFC516KC1234>

Technical Specifications

Brand	Minerallac
Item	Conduit hanger assembly
Mount Type	Hammer-on flange clamp
Hanger Type	Spring clip
Mount Side	Back
Material	Spring steel
Finish	Zinc phosphate plated
Minimum Flange Thickness	5/16in
Maximum Flange Thickness	1/2in
Load Rating	25 lbs
Outside Diameter	0.70in-1.05in
Tubing Size	3/4in, 13/16in, 7/8in, 15/16in and 1in

Rigid Metallic Conduit (RMC) Trade Size	1/2in and 3/4in
Electrical Metallic Tubing (EMT) Trade Size	1/2in and 3/4in
Intermediate Metallic Conduit (IMC) Trade Size	1/2in and 3/4in
Reduced Wall Flexible Metal Conduit Trade Size	3/8in and 1/2in
Liquid-tight Flexible Metal Conduit (LFMC) Trade Size	1/2in and 3/4in
UL Type	UL 2239
Quantity per Pack	100
For Use With	5/16 to 1/2in flanges and 1/2 or 3/4in conduit

Agency Approvals

UL Listed File #	E165884
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document