

# SFP-30K-FSF Cut Sheet

STRIDE 100 Mbps small form factor pluggable (SFP) transceiver module, 1310nm, 30km, single-mode fiber, Duplex LC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFP-30K-FSF>

## Technical Specifications

Brand	STRIDE
Item	Transceiver module
Data Rate	100 Mbps
Small Form Factor Pluggable (SFP)	Yes
Light Source	1310nm
Transmission Distance	30km
Modes	Single-mode fiber
Receptacle Type	Duplex LC
Additional Information	SFP Multi-Source Agreement compliant

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SFP-30K-FSF.pdf>  
See store item page for other formats.