

# SFP-4K-FMF Cut Sheet



STRIDE 100Mbps small form factor pluggable (SFP) transceiver module, 1310nm, 4km, multi-mode fiber, Duplex LC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFP-4K-FMF>

## Technical Specifications

Brand	STRIDE
Item	Transceiver module
Data Rate	100Mbps
Small Form Factor Pluggable (SFP)	Yes
Light Source	1310nm
Transmission Distance	4km
Modes	Multi-mode fiber
Receptacle Type	Duplex LC
Additional Information	SFP Multi-Source Agreement compliant

## Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>