

SFP-500-GMF Cut Sheet

STRIDE Gigabit (1.25 Gb) small form factor pluggable (SFP) transceiver module, 850nm, 550m, multi-mode fiber, Duplex LC.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SFP-500-GMF>

Technical Specifications

Brand	STRIDE
Item	Transceiver module
Data Rate	Gigabit (1.25 Gb)
Small Form Factor Pluggable (SFP)	Yes
Light Source	850nm
Transmission Distance	550m
Modes	Multi-mode fiber
Receptacle Type	Duplex LC
Additional Information	SFP Multi-Source Agreement compliant

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SFP-500-GMF.pdf>
See store item page for other formats.