

SG3A0075KB Cut Sheet



Hammond general purpose transformer, open core, 75 kVA, 3-phase, 480 VAC Delta primary, 208Y/120 VAC secondary, 60 Hz, NEMA 3R, floor mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SG3A0075KB>

Technical Specifications

Brand	Hammond
Series	Sentinel
Item	Transformer
Transformer Type	General purpose
Core Type	Open
Power Rating	75 kVA
Number of Phases	3
Primary Voltage	480 VAC Delta

Secondary Voltage	208Y/120 VAC
Frequency	60 Hz
Fused	No
Electrostatic Shield	No
NEMA Rating	3R
Mounting	Floor
Connection	Box lug

Agency Approvals

UL Listed File #	E112313
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR3902
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/SG3A0075KB.pdf>
See store item page for other formats.