

# SG3C0015KD Cut Sheet



Hammond general purpose transformer, open core, 15 kVA, 3-phase, 480 VAC Delta primary, 240/120 VAC Delta (center tap) secondary, 60 Hz, NEMA 3R, floor, wall or ceiling mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SG3C0015KD>

## Technical Specifications

Brand	Hammond	Secondary Voltage	240/120 VAC Delta (center tap)
Series	Sentinel	Frequency	60 Hz
Item	Transformer	Fused	No
Transformer Type	General purpose	Electrostatic Shield	No
Core Type	Open	NEMA Rating	3R
Power Rating	15 kVA	Mounting	Floor, wall or ceiling
Number of Phases	3	Connection	Box lug
Primary Voltage	480 VAC Delta		

## Agency Approvals

UL Listed File #	E112313
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR3902
RoHS Status	No
EU REACH	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SG3C0015KD.pdf>  
See store item page for other formats.