

# SG3C0030KD Cut Sheet



Hammond general purpose transformer, open core, 30 kVA, 3-phase, 480 VAC Delta primary, 240/120 VAC Delta (center tap) secondary, 60 Hz, NEMA 3R, floor, wall or ceiling mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SG3C0030KD>

## Technical Specifications

<b>Brand</b>	Hammond
<b>Series</b>	Sentinel
<b>Item</b>	Transformer
<b>Transformer Type</b>	General purpose
<b>Core Type</b>	Open
<b>Power Rating</b>	30 kVA
<b>Number of Phases</b>	3
<b>Primary Voltage</b>	480 VAC Delta

<b>Secondary Voltage</b>	240/120 VAC Delta (center tap)
<b>Frequency</b>	60 Hz
<b>Fused</b>	No
<b>Electrostatic Shield</b>	No
<b>NEMA Rating</b>	3R
<b>Mounting</b>	Floor, wall or ceiling
<b>Connection</b>	Box lug

## Agency Approvals

<b>UL Listed File #</b>	E112313
<b>UL Recognized File #</b>	None
<b>UL Hazardous File #</b>	None
<b>CE</b>	None
<b>CSA File #</b>	LR3902
<b>RoHS Status</b>	No
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SG3C0030KD.pdf>  
See store item page for other formats.