

SG3C0045KD Cut Sheet



Hammond general purpose transformer, open core, 45 kVA, 3-phase, 480 VAC Delta primary, 240/120 VAC Delta (center tap) secondary, 60 Hz, NEMA 3R, floor, wall or ceiling mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SG3C0045KD>

Technical Specifications

Brand	Hammond
Series	Sentinel
Item	Transformer
Transformer Type	General purpose
Core Type	Open
Power Rating	45 kVA
Number of Phases	3
Primary Voltage	480 VAC Delta
Secondary Voltage	240/120 VAC Delta (center tap)
Frequency	60 Hz
Electrostatic Shield	No
NEMA Rating	3R
Mounting	Floor, wall or ceiling

Agency Approvals

UL Listed File #	E112313
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	LR3902
RoHS Status	No
EU REACH	View EU REACH document