

SHDS-88C-40-42 Cut Sheet



Sung-II Machinery drive coupling, high torque disc, 7075-T6 aluminum alloy, clamp, size 88, 40 x 42mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHDS-88C-40-42>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	High torque disc
Material	7075-T6 aluminum alloy
Rated Torque	180 N·m
Maximum Torque	360 N·m
Maximum Angular Misalignment	0.7 degrees
Maximum Parallel Misalignment	0.02mm
Maximum RPM	5500

Attachment Style	Clamp
Coupling Size	88
Overall Length	69.9mm
Bore Diameter	40mm
Bore Diameter 2	42mm
Outside Diameter	88mm
Clamp Screw Fastening Torque	30 N·m
Clamp Screw Size	M8-1.25 x 25mm

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SHDS-88C-40-42.pdf>
See store item page for other formats.