

SHR-43C-19.05-19.05 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 43, 3/4 x 3/4in bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-43C-19.05-19.05>

Technical Specifications

| | |
|--------------------------------------|-------------------|
| Brand | Sung-II Machinery |
| Item | Drive coupling |
| Coupling Type | Servo high gain |
| Material | Aluminum alloy |
| Rated Torque | 16 N·m |
| Maximum Torque | 32 N·m |
| Maximum Angular Misalignment | 1.5 degrees |
| Maximum Parallel Misalignment | 0.2mm |
| Maximum RPM | 14000 |

| | |
|-------------------------------------|---------------|
| Attachment Style | Clamp |
| Coupling Size | 43 |
| Overall Length | 48mm |
| Bore Diameter | 3/4in |
| Bore Diameter 2 | 3/4in |
| Outside Diameter | 42.8mm |
| Clamp Screw Fastening Torque | 3.7 N·m |
| Clamp Screw Size | M4-0.7 x 14mm |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/SHR-43C-19.05-19.05.pdf>
See store item page for other formats.