

SHR-55C-24-25 Cut Sheet



Sung-II Machinery drive coupling, servo high gain, aluminum alloy, clamp, size 55, 24 x 25mm bore.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SHR-55C-24-25>

Technical Specifications

Brand	Sung-II Machinery
Item	Drive coupling
Coupling Type	Servo high gain
Material	Aluminum alloy
Rated Torque	31.5 N-m
Maximum Torque	63 N-m
Maximum Angular Misalignment	1.5 degrees
Maximum Parallel Misalignment	0.2mm
Maximum RPM	11000
Attachment Style	Clamp
Coupling Size	55
Bore Diameter	24mm
Bore Diameter 2	25mm
Outside Diameter	54.8mm
Clamp Screw Fastening Torque	8.5 N-m
Clamp Screw Size	M55

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	RoHS Statement